




XT IEC Power Control

Quick Reference Guide

**Contactors
Starters
Manual Motor
Protectors**





Also available (not shown):

- **XT** Mini Contactors, 6-9A
- **XT** Contactors up to 2000A
- **XT** Overload Relays up to 630A

XT Manual Motor Protectors

						
Catalog Number Selection	kW@ 400V	Max hp @ 460V	Amp Range	Pushbutton B-Frame	Rotary B-Frame	Rotary D-Frame
Example: XTPB P16 B C1 Prefix Frame Size Max Overload Setting Trip Class C1 = 10	①	①	0.1 – 0.16	XTPBP16BC1	XTPRP16BC1	
	0.06	①	0.16 – 0.25	XTPBP25BC1	XTPRP25BC1	
	0.09	①	0.25 – 0.40	XTPBP40BC1	XTPRP40BC1	
	0.12	①	0.40 – 0.63	XTPBP63BC1	XTPRP63BC1	
	0.25	1/2	0.63 – 1.0	XTPB001BC1	XTPR001BC1	
	0.55	3/4	1.0 – 1.6	XTPB1P6BC1	XTPR1P6BC1	
	0.75	1	1.6 – 2.5	XTPB2P5BC1	XTPR2P5BC1	
	1.5	2	2.5 – 4.0	XTPB004BC1	XTPR004BC1	
	2.2	3	4.0 – 6.3	XTPB6P3BC1	XTPR6P3BC1	
	4.0	7-1/2	6.3 – 10	XTPB010BC1	XTPR010BC1	
	5.5	7-1/2	8 – 12	XTPB012BC1	—	
	7.5	10	9 – 12	—	XTPR012BC1	
	7.5	10	10 – 16	XTPB016BC1	XTPR016BC1	XTPR016DC1
	9.0	10	16 – 20	XTPB020BC1	XTPR020BC1	XTPR025DC1
	12.5	15	20 – 25	XTPB025BC1	XTPR025BC1	XTPR025DC1
	15	25	25 – 32		XTPR032BC1	XTPR032DC1
	20	30	32 – 40			XTPR040DC1
	25	30②	40 – 50			XTPR050DC1
	30	40②	50 – 58			XTPR058DC1
	34	—	55 – 65			XTPR063DC1
Width			mm	45	45	55
Height			mm	93	93	140
Depth			mm	90.5	76	160
Auxiliary contact modules, front mount				XTPAXFA_③		
Auxiliary contact modules, side mount				XTPAXSA_③		
Short circuit breaking capacity I _{cu} at 10A / 400V			kA	50 AC/60 DC	150 AC/60 DC	—
Short circuit breaking capacity I _{cu} at 12A / 400V			kA	50 AC/60 DC	50 AC/60 DC	—
Short circuit breaking capacity I _{cu} at 25A / 400V			kA	50 AC/60 DC	50 AC/40 DC	150 AC/60 DC
Short circuit breaking capacity I _{cu} at 32A / 400V			kA	—	50 AC/40 DC	50 AC/60 DC
Short circuit breaking capacity I _{cu} at 65A / 400V			kA	—	—	50 AC/60 DC
Electrical lifespan			Operations	50,000	100,000	30,000
Single-phasing sensitivity				yes	yes	yes
Undervoltage release				XTPAXUVR120V60H④		
Shunt release				XTPAXSR120V60H④		
Three-phase commoning link (number of MMPs on bus bar)			MMPs only	2 – 5	2 – 5	2 – 4
			With 1 aux	2 – 5	2 – 5	2 – 4
			With 2 aux	2 or 4	2 or 4	2 or 4

① Use motor current for sizing.

② Consult Eaton for availability.

③ Consult catalog for available auxiliary contact configurations.

④ Consult catalog for other voltage options.

General Applications

Enclosed manual motor protectors (MMPs) are often specified for small fans and blower motors in commercial and industrial applications. OEM opportunities include woodworking machinery, small machine tools, pumps and compressors.


Group Motor Applications

XT manual motor protectors are UL listed for group motor installations. A group motor installation consists of two or more motor circuits protected by a single set of fuses or circuit breaker. This eliminates the need for individual branch fusing or circuit protection.

The reduced cost of components, panel size, wiring, assembly charges and labor are substantial with group motor installations.



Consult NEC Article 430-52 for sizing the branch circuit protective device for a group motor application.

XT IEC
Power Control

XT IEC Power Control		Frame Size A				Frame Size B								Frame Size C						Frame Size D				Frame Size F				Frame Size G																					
																																																	
Contactor: Basic Catalog Number		XTMC6A		XTMC9A		XTCE007B		XTCE009B		XTCE012B		XTCE015B		XTCE018C		XTCE025C		XTCE032C		XTCE040D		XTCE050D		XTCE065D		XTCE080F		XTCE095F		XTCE115G		XTCE150G																	
Current Ratings (I) IEC 60947-4-1 AC-1 Thermal Current I _{th}		20 Amperes		20 Amperes		20 Amperes		20 Amperes		20 Amperes		20 Amperes		35 Amperes		40 Amperes		40 Amperes		50 Amperes		60 Amperes		72 Amperes		110 Amperes		110 Amperes		160 Amperes		160 Amperes																	
AC-3 Operational Power Ratings I _e		kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp																
200V		—	1-1/2	—	2	—	1-1/2	—	3	—	3	—	5	—	5	—	7-1/2	—	10	—	10	—	15	—	20	—	25	—	25	—	40	—	40																
220/230V		1.5	2	2.2	3	2.2	2	2.5	3	3.5	3	4	5	5	5	7.5	7-1/2	10	10	12.5	15	15.5	20	20	25	25	30	30	40	37	50	48	60																
380/400V		3	—	4	—	3	—	4	—	5.5	—	7.5	—	7.5	—	11	—	15	—	18.5	—	22	—	30	—	37	—	45	—	55	—	75	—																
460V		—	3	—	5	—	3	—	5	—	10	—	10	—	10	—	15	—	20	—	30	—	40	—	50	—	60	—	75	—	100	—	125																
575V		—	3	—	5	—	5	—	7-1/2	—	10	—	10	—	15	—	20	—	25	—	40	—	50	—	60	—	75	—	100	—	125	—	125																
660/690V ®		3	—	4	—	3.5	—	4.5	—	6.5	—	7	—	11	—	14	—	17	—	23	—	30	—	35	—	63	—	75	—	90	—	96	—																
1000V ®		—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—																	
Built-in Auxiliary Contacts		10 = 1NO 01 = 1NC																		00 = 0NO-0NC																													
Coil Options		Coil Voltage 110V 50 Hz, 120V 60 Hz 220V 50 Hz, 240V 60 Hz 230V 50 Hz 24V 50/60 Hz 24V DC				Code A B F T TD®		Coil Voltage 415V 50 Hz, 480V 60 Hz 550V 50 Hz, 600V 60 Hz 208V 60 Hz 190V 50 Hz, 220V 60 Hz 240V 50 Hz, 277V 60 Hz 380V 50 Hz, 440V 60 Hz				Code C D E G H L		Coil Voltage 400V 50 Hz 380V 60 Hz 12V 50/60 Hz 24V 50 Hz 42V 50 Hz, 48V 60 Hz 48V 50 Hz				Code N P R U W Y		Coil Voltage 110V 50 Hz, 120V 60 Hz 220V 50 Hz, 240V 60 Hz 230V 50 Hz 24V 50/60 Hz 24 – 27V DC				Code A B F T TD®		Coil Voltage 415V 50 Hz, 480V 60 Hz 550V 50 Hz, 600V 60 Hz 208V 60 Hz 190V 50 Hz, 220V 60 Hz 240V 50 Hz, 277V 60 Hz 380V 50 Hz, 440V 60 Hz				Code C D E G H L		Coil Voltage 400V 50 Hz 380V 60 Hz 12V 50/60 Hz 24V 50 Hz 42V 50 Hz, 48V 60 Hz* 48V 50 Hz				Code N P R U W Y		Coil Voltage 100 – 120V 50/60 Hz 190 – 240V 50/60 Hz 24V 50/60 Hz 24 – 27V DC 480 – 500V 50/60 Hz 380 – 440V 50/60 Hz				Code A B T TD® C L		Coil Voltage 42 – 48V 50/60 Hz 110 – 130V DC 200 – 240V DC 48 – 60V DC				Code W AD® BD® WD®	
AC Magnet Coil Data																																																	
Pick-Up VA		50/60 Hz		25		25		24 – 29		24 – 29		24 – 29		24 – 29		50 – 62		50 – 62		50 – 62		150 – 185		150 – 185		150 – 185		310 – 375		310 – 375		130		130															
Sealed VA		50/60 Hz		4.6		4.6		4.0 – 4.4		4.0 – 4.4		4.0 – 4.4		4.0 – 4.4		8.0 – 9.1		8.0 – 9.1		8.0 – 9.1		16.0 – 19.0		16.0 – 19.0		16.0 – 19.0		26.0 – 31.0		26.0 – 31.0		3.5		3.5															
Wire Ranges		AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²														
Main Cable ®		18 – 14	1 x (0.75-1.5) 2 x (0.75-1.5)	18 – 14	1 x (0.75-1.5) 2 x (0.75-1.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 6	1 x (0.75-16) 2 x (0.75-10)	18 – 6	1 x (0.75-16) 2 x (0.75-10)	18 – 6	1 x (0.75-16) 2 x (0.75-10)	12 – 2	1 x (2.5-35) 2 x (2.5-25)	12 – 2	1 x (2.5-35) 2 x (2.5-25)	12 – 2	1 x (2.5-35) 2 x (2.5-25)	8 – 250MCM	1 x (10-95) 2 x (10-70)	8 – 250MCM	1 x (10-95) 2 x (10-70)	8 – 3/0	1 x (10-95) 6 – 2/0	8 – 3/0	1 x (10-95) 2 x (10-70)																
Control Circuits ®		18 – 14	1 x (0.75-1.5) 2 x (0.75-1.5)	18 – 14	1 x (0.75-1.5) 2 x (0.75-1.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-2.5)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)	18 – 14	1 x (0.75-4) 2 x (0.75-4)																
Auxiliary Contacts		 XTMCX F A C 02 [F = Front mount] Blank = Screw terminals C = Spring cage terminals 02 = 2NC 20 = 2NO 04 = 4NC 22 = 2NO-2NC 11 = 1NO-1NC 31 = 3NO-1NC 13 = 1NO-3NC 40 = 4NO				 XTCEX F A C C 11 [F = Front mount] C = Frames B – C Blank = Screw terminals C = Spring cage terminals A = seq A AL = seq AL C = seq C CL = seq CL D = seq D 02 = 2NC 04 = 4NC 11 = 1NO-1NC 13 = 1NO-3NC 20 = 2NO 22 = 2NO-2NC 31 = 3NO-1NC 40 = 4NO								 XTCEX F A G C 22 [F = Front mount S = Side mount] A = seq A B = seq B BL = seq BL Blank = Screw terminals C = Spring cage terminals G = Front mount, frames D-G N = Side mount, frames D-N 02 = 2NC 04 = 4NC 11 = 1NO-1NC 13 = 1NO-3NC 20 = 2NO 22 = 2NO-2NC 31 = 3NO-1NC 40 = 4NO																																			
Overload Relay		 XTOM 004 A C1 P16 = 0.10 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.40A P60 = 0.40 – 0.60A 001 = 0.60 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 009 = 6 – 10A 012 = 9 – 12A C1 = Class 10				 XTOB 001 B C1 P16 = 0.10 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.40A P60 = 0.40 – 0.60A 001 = 0.60 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 012 = 9 – 12A 016 = 12 – 16A C1 = Class 10								 XTOB 010 C C1 P16 = 0.10 – 0.16A P24 = 0.16 – 0.24A P40 = 0.24 – 0.40A P60 = 0.40 – 0.60A 001 = 0.60 – 1A 1P6 = 1.0 – 1.6A 2P4 = 1.6 – 2.4A 004 = 2.4 – 4A 006 = 4 – 6A 010 = 6 – 10A 012 = 9 – 12A 024 = 16 – 24A 032 = 24 – 32A C1 = Class 10						 XTOB 040 D C1 010 = 6 – 10A 016 = 10 – 16A 024 = 16 – 24A 040 = 24 – 40A 057 = 40 – 57A 065 = 50 – 65A C1 = Class 10				 XTOB 100 F C1 035 = 25 – 35A 050 = 35 – 50A 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A G-frame only 150 = 120 – 150A F = 80 – 95A G = 115 – 150A C1 = Class 10																									
Catalog Numbering System		Mini Contactors Example:  XTMC 6 A 01 A XT Non-reversing Mini Contactor Amp Rating Frame Auxiliary Contact Configuration Coil Code																Contactors Example:  XTCE 007 B 01 A XT Non-reversing Contactor Amp Rating Frame Auxiliary Contact Configuration Coil Code								Starters Example:  XTAE 007 B 10 A 004 XT Non-reversing Starter Amp Rating Frame Coil Code Overload Relay Amp Range																							

® For 185 – 2000A Contactors at 660/690V or 1000V: Do not reverse directly. ® 7 – 65A — flexible with ferrule cable, 185 – 2000A — flexible with cable lug. ® Flexible with ferrule cable. ®With DC Operation: Integrated diode-resistor combination, coil rating 2.6W. ®Contact Eaton for availability.

XT IEC
Power Control

XT IEC Power Control	Frame Size L						Frame Size M						Frame Size N						Frame Size P		Frame Size R					
																										
Contactor: Basic Catalog Number	XTCE185L		XTCE225L		XTCE250L		XTCE300M		XTCE400M		XTCE500M		XTCE580N		XTCE650N		XTCE750N		XTCE820N		XTCEC10N		XTCEC14P		XTCEC20R	
Current Ratings (I) IEC 60947-4-1 AC-1 Thermal Current I _{th}	275 Amperes		315 Amperes		350 Amperes		400 Amperes		500 Amperes		700 Amperes		800 Amperes		850 Amperes		900 Amperes		1000 Amperes		1000 Amperes		1400 Amperes		2000 Amperes	
AC-3 Operational Power Ratings I _e	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp	kW	hp
200V	—	50	—	60	—	75	—	100	—	125	—	150	—	200	—	200	—	250	—	290	—	—	—	—	—	—
220/230V	55	60	70	75	75	100	90	125	125	150	155	200	185	200	205	250	240	300	260	350	315	—	—	—	—	
380/400V	90	—	110	—	132	—	160	—	200	—	250	—	315	—	355	—	400	—	450	—	560	—	—	—	—	—
460V	—	125	—	150	—	200	—	250	—	300	—	400	—	400	—	500	—	600	—	700	—	—	—	—	—	—
575V	—	150	—	200	—	250	—	300	—	400	—	500	—	600	—	600	—	700	—	860	—	—	—	—	—	—
660/690V ⑥	175	—	215	—	240	—	286	—	344	—	344	—	516	—	630	—	720	—	750	—	1000	—	—	—	—	—
1000V ⑥	108	—	108	—	108	—	132	—	132	—	132	—	600	—	600	—	800	—	800	—	1000	—	—	—	—	—
Built-in Auxiliary Contacts	22 = 2NO-2NC																									
Coil Options	Coil Voltage 110 – 250V 40 – 60 Hz AC/DC 250 – 500V 40 – 60 Hz AC/DC 48 – 110V 40 – 60 Hz AC/DC 24 – 48V AC/DC Code A C Y® TD®																						Coil Voltage 220 – 250V 50/60 Hz DC Code B			
AC Magnet Coil Data																										
Pick-Up VA 50/60 Hz	250		250		250		450		450		450		800		800		800		800		800		800		1600	
Sealed VA 50/60 Hz	4.3		4.3		4.3		4.3		4.3		4.3		7.5		7.5		7.5		7.5		7.5		7.5		15	
Wire Ranges	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²	AWG	mm²
Main Cable ⑥	1/0-250MCM	50-240	1/0-250MCM	50-240	1/0-250MCM	50-240	1/0-250MCM	50-240	1/0-250MCM	50-240	1/0-250MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240	2/0-500MCM	50-240
Control Circuits ⑥	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)	2 x (18-12)	1 x (0.75-2.5) 2 x (0.75-2.5)
Auxiliary Contacts	 XTCEX F S = Side mount B B = seq B BL = seq BL N N = Frames D – N C Blank = Screw terminals C = Spring cage terminals 11 11 = 1NO-1NC																									
Overload Relay	XTOB 125 L C1 070 = 50 – 70A 100 = 70 – 100A 125 = 95 – 125A 160 = 120 – 160A 220 = 160 – 220A 250 = 200 – 250A C1 = Class 10						 XTOT 160 C3 S 063 = 42 – 63A 090 = 60 – 90A 125 = 85 – 125A 160 = 110 – 160A 240 = 160 – 240A 290 = 190 – 290A 400 = 270 – 400A 540 = 360 – 540A 630 = 420 – 630A C3 = Class 30 S = Separate mounting only for XTOT																			
Catalog Numbering System	Contactors Example: XTCE 185 L 22 A XT Non-reversing Contactor Amp Rating Frame Auxiliary Contact Configuration Coil Code Starters Example: XTAE 250 L 22 A 004 XT Non-reversing Starter Amp Rating Frame Auxiliary Contact Configuration Coil Code Overload Relay Amp Range																									

® For 185 – 2000A Contactors at 660/690V or 1000V: Do not reverse directly. ® 7 – 65A — flexible with ferrule cable, 185 – 2000A — flexible with cable lug. ® Flexible with ferrule cable. ®With DC Operation: Integrated diode-resistor combination, coil rating 2.6W.



Eaton's electrical business is a global leader in electrical control, power distribution, and industrial automation products and services. Through advanced product development, world-class manufacturing methods, and global engineering services and support, Eaton's electrical business provides customer-driven solutions under brand names such as Cutler-Hammer®, Powerware®, Durant®, Heinemann®, Holec® and MEM®, which globally serve the changing needs of the industrial, utility, light commercial, residential, and OEM markets. For more information, visit www.EatonElectrical.com.

Eaton Corporation is a diversified industrial manufacturer with 2006 sales of \$12.4 billion. Eaton is a global leader in electrical systems and components for power quality, distribution and control; fluid power systems and services for industrial, mobile and aircraft equipment; intelligent truck drivetrain systems for safety and fuel economy; and automotive engine air management systems, powertrain solutions and specialty controls for performance, fuel economy and safety. Eaton has 60,000 employees and sells products to customers in more than 125 countries. For more information, visit www.eaton.com.

Eaton Electrical Inc.

1000 Cherrington Parkway
Moon Township, PA 15108
United States

For more information or to locate regional product support,
please visit us at: www.EatonElectrical.com

