# PARDUIT®



CABLE TIES
Product Selection Guide

# **Comprehensive Cable Tie Solutions**

Panduit offers a broad selection of industry approved styles, sizes, and materials to meet a full range of electrical, industrial, and networking applications.

PLT Pan-Ty® Cable Ties

Most comprehensive product offering

SG Super-Grip® Cable Ties Withstand rough installations

BT Dome-Top® Barb Ty Cable Ties Metal locking barb; infinite adjustability

DT Dura-Ty® Cable Ties

Acetal material; 20+ years outdoor service life

**CBR Contour-Ty® Cable Ties** 

Low profile head, parallel-entry, outside teeth

**HV** Hyper-V<sup>™</sup> Cable Ties

Teeth on both sides; 2-wedge locking design

SST Sta-Strap® Cable Ties

Two-piece design, low thread force, lightweight

**ERT Elastomeric Cable Ties** 

Flexible, elastic material, UL 94V-0, releasable

			TO VE	No.			Pan		
	Product Family	PLT	SG	BT	DT	CBR	HV	SST	ERT
	Locking	✓	✓	✓	✓	✓	✓	✓	
100	Releasable	✓							✓
les	Marker	✓		✓				✓	
Styles	Clamp	✓		✓				✓	
	Push Mount	$\checkmark$		✓					
	Specialty	✓		✓				✓	
(0)	Miniature	✓	✓	✓		✓		✓	✓
Sections	Intermediate	✓	✓	✓		✓		✓	
cţi	Standard	✓	✓	✓		✓		✓	
Se	Heavy-Standard					✓			
	Light-Heavy	✓	✓	✓		✓	✓		
Cross	Heavy	✓	✓		✓			✓	
	Extra-Heavy	✓			✓				

## **Cable Tie Industry Approvals**

Agency	Spec/Approval	Requirement	Products					
UL (Underwriters Laboratory	UL 62275 (File E56854)	Types 1, 11, 2, 2S, 21, 21S (Note 1)	Select PLT, BT, SG, SST, and CBR Series					
CSA (Canadian Standards Association)	CSA-C22.2 No. 62275 (File 31212)	Types 1, 11, 2, 2S, 21, 21S (Note 1)	Select PLT, BT, SG, SST, and CBR Series					
ABS (American Bureau of Shipping)	05-HS463235-PDA	2005 Steel Vessel Rules 1-1-4/7.7,4-8-4/21.9.32001 MODU Rules 4-3-3/5.9.1	PLT and BT Series					
Bureau Veritas	Cert 05968/C0, BV File ACE 14/601/01 Product Code: 2535H	Bureau Veritas Rules for the Classification of Steel Ships	PLT, PRT, BT and CBR Series					
Det Norske Veritas	E-6405	Det Norske Veritas' Rules for Classification of Ships and Mobile Offshore Units	PLT, PLC, PLM, PRT, PLWP, PRWP and PRST Series					
Lloyd's Register of Shipping	89/60111 (E3)	Lloyd's Register Type Approval	PLT, PLC, PLP, PLWP, PLM, PRT, SST, SSC, SSM, BT, BC, BM, BF, B2M, B3M, BM, BW, BP, ILT and CBR Series					
Russian Maritime Register of Shipping	11130200	Russian Maritime Type Approval Certificate	PLT, PLC, PLM, PLF, SG, BT, BF, BM, BC, DT and CBR Series					
NRC (Nuclear Regulatory Commission)	NRC 10CFR50	Quality Assurance Criteria for Nuclear	All cable tie products					
US Military Aerospace Standard	QPL-AS23190	SAE spec AS23190	Select PLT, BT, SST, and CBR Series					

# **Material Selection Criteria**

	Material	Test Method	Nylon 6.6	Weather Resistant Nylon 6.6	Impact Modified Weather Resistant Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Nylon 6.6	Heat Stabilized Weather Resistant Nylon 6.6	Flame Retardant Nylon 6.6
	Color	_	Natural (other colors available)	Black	Black	Black	Natural	Black	Black
	Part Number Suffix (Material Designation)	_	No Suffix	0	0	30	39	300	60
	Tensile @ Yield @ 73°F (psi)	ISO 527	12,000	12,000	9,700	12,000	12,000	12,000	11,000
ical	Water Absorption (24 Hours)	ASTM D570	1.2%	1.2%	1.2%	1.2%	1.2%	1.2%	1.1%
char	Radiation Resistance (Rads) Weathering Life Expectancy	_	1 x 10 <sup>5</sup>	1 x 10⁵	1 x 10⁵	1 x 10 <sup>5</sup>	1 x 10⁵	1 x 10 <sup>5</sup>	1 x 10 <sup>5</sup>
₽₽	Weathering Life Expectancy (Years)/UV Resistance	_	1 – 2	7 – 9	7 – 9	4 – 5	1 – 2	7 – 9	1 – 2
	Impact Resistance	_							
	Salts	_							
cal	Hydrocarbons (Oil, Lubricants) Chlorinated Hydrocarbons Acids	_	•	•	•	•	•	•	
sta	Chlorinated Hydrocarbons	_							
Che	Acids	_							
- #	Bases	_							
	Acid Rain	_							
	Continuous Use Temperature Range	UL 746B	-76°F – 185°F -60°C – 85°C	-76°F – 185°F -60°C – 85°C			-76°F – 239°F -60°C – 115°C		-76°F – 212°F -60°C – 100°C
perties	Minimum Installation Temperature	UL 62275	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)	-4°F or +32°F -20°C or 0°C (Note 1)
obe	Flammability Rating	UL 94	V-2	V-2	НВ	V-2	V-2	V-2	V-0
al Pro	Low Smoke	ASTM E662	PASS	PASS	PASS	PASS	PASS	PASS	PASS
herm	Oxygen Index	BS ISO 4589	28	28	_	28	28	28	34
F	Halogen-Free	IEC 60754-2	Yes	Yes	Yes	Yes	Yes	Yes	Yes
	Burning Fume Toxicity	BSS-7239	PASS	PASS	PASS	PASS	PASS	PASS	PASS
	Heat Deflection Temperature @ 1.8 Mpa	ASTM D648 ISO 75 -1/-2	158°F 70°C	158°F 70°C	145°F 63°C	158°F 70°C	158°F 70°C	158°F 70°C	154°F 68°C
	Relative Price		Low	Low	Low	Low	Low	Med	Med
	Product Family			Cross Se	notions				
	Product Family Pan-Ty® Cable Ties PLT			SM, M, I, S	LH, H, EH	,	,	,	,
-	•		<i>J</i>	M, I, S, LH	Н	✓ ✓	✓	✓	✓
ability	Dome-Top® Barb Ty Cable TiesBT		<b>√</b>	M, I, S	LH	<b>✓</b>	/	/	
Availab	Dura-Ty™ Cable Ties DT					-		*	
	Contour-Ty® Cable Ties CBR		✓	M, I, S, HS, LH		<b>✓</b>	<b>√</b>		
Materia	Hyper-V™ Cable Ties HV				LH				
	Sta-Strap® Cable Ties SST		✓	M, I, S, H		✓			
	Elastomeric Cable Ties ERT								

	Recommendation Legend								
Highest	Highest High Acceptable Low Lowest								
		0	•						

Check mark indicates material availability in that product family for all cross sections.

Cross Sections: SM = Subminiature, M = Miniature, I = Intermediate, S = Standard, HS = Heavy-Standard, LH = Light-Heavy, H = Heavy, EH = Extra-Heavy

Flame	Weather		Weather				Metal	Metal	DT Weather	ERT Flame
Retardant	Resistant		Resistant				Detectable	Detectable		Retardant
Nylon 6.6			Polypropylene		HALAR*	PEEK	Nylon	Polypropylene		TPU
Natural Ivory	Black	Green	Black	Aqua Blue	Maroon	Translucent Brown	Lt. Blue	Dark Blue	Black	Black
69	120	109	100	76	702Y	71	86	186	N/A	20
11,000	6,700	4,100	4,100	7,500	7,000	15,200	_	-	6,500	4,300
1.1%	0.3%	0.1%	0.1%	<0.03%	<0.05%	0.5%	1.2%	0.1%	<0.45%	0.25%
1 x 10⁵	3.5 x 10 <sup>6</sup>	1 x 10 <sup>6</sup>	1 x 10 <sup>6</sup>	2 x 10 <sup>8</sup>	2 x 10 <sup>8</sup>	1 x 10 <sup>9</sup>	_	1 x 10 <sup>6</sup>	6 x 10⁵	_
1 – 2	12 – 15	1	7 – 9	>15	>15	_	_	1	>20	7 – 9
	0		<b>-</b>				0			
									0	
•	•	0	0	•	•	•	•	0	•	0
		0	0					0		
-76°F – 212°F -60°C – 100°C	-76°F – 194°F -60°C – 90°C		-76°F – 239°F -60°C – 115°C	-76°F – 338°F -60°C – 170°C		-76°F – 500°F -60°C – 260°C (Note 2)	-76°F – 185°F -60°C – 85°C	-76°F – 239°F -60°C – 115°C	76°F – 185°F -60°C – 85°C	-40°F – 122°F -40°C – 50°C
-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F	-4°F or +32°F
-20°C or 0°C	-20°C or 0°C	-20°C or 0°C	-20°C or 0°C	-20°C or 0°C		-20°C or 0°C	-20°C or 0°C	-20°C or 0°C	-20°C or 0°C	
(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)	(Note 1)
V-0	HB	HB	HB	V-0	V-0	V-0	HB	HB	НВ	V-0
PASS	_	_	_	_	_	PASS	_	_	PASS	_
34	_	_	_	30	52	35	_		_	26
Yes	Yes	Yes	Yes	No	No	Yes	Yes	Yes	Yes	Yes
PASS	_	_	_			_	_	_	_	_
154°F 68°C	122°F 50°C	122°F 50°C	122°F 50°C	_	149°F 65°C	313°F 156°C	_	_	147°F 64°C	_
Med	Med	Med	Med	High	High	High	Low	Med	Med	High
		T								
,	,			,			,			
✓	<b>✓</b>	<b>✓</b>	✓	✓	✓	✓	<b>✓</b>	✓		
,										
<b>/</b>									_	
									/	
✓										
										✓

Note 1: Check UL file for specific part number rating Note 2: Based upon UL RTI for electrical properties

<sup>■</sup>TEFZEL is a registered trademark of E.I. du Pont de Nemours and Company.

<sup>▲</sup>HALAR is a registered trademark of Ausimont USA, Inc.

## **Cable Tie Installation Tools**

Panduit offers the most preferred hand-operated tools in the industry. These versatile tools can be used for production, maintenance or construction applications. Panduit cable tie installation tools promote worker safety, help reduce downtime, improve productivity and provide the lowest total installed cost. As with all Panduit products, quality in design and production along with customer service excellence, are assured.

#### Cable Tie Tools



**GTS** 

- Used with SM, M, I, and S cable ties
- Ergonomic design with impact resistant resin housing, narrow nose, and cushion handle



**GTSL** 

- Used with SM, M, I, and S cable ties
- Ergonomic design with impact resistant resin housing, narrow nose, and cushion handle. Shorter handle reach (than GTS) for users with small hands



GS2B

- Used with M, I, and S cable ties
- Metal tool with a durable powder coat finish



**GTH** 

- Used with S, HS, LH, and H cable ties
- Ergonomic design with impact resistant resin housing, narrow nose, and cushion handle



GS4H

- Used with S, HS, LH, and H cable ties
- Metal tool with a durable powder coat finish



GS4EH

- Used with LH, H, and EH cable ties
- Metal tool with a durable powder coat finish

## **Pneumatic Hand Tools**



**PTS** 

- Used with SM, M, I, and S cable ties
- Ergonomic design with impact resistant resin housing and black knob; replacement parts can be part of a scheduled maintenance program



**PTH** 

- Used with S, HS, LH, and H cable ties
- Ergonomic design with impact resistant resin housing and red knob; replacement parts can be part of a scheduled maintenance program



**Pneumatic Tool Accessories** 

 Visit www.panduit.com for our complete line of pneumatic tool accessories

# **Complete Your Bundling System**

### **Tools**



#### **Manual Cable Tie Installation Tools**

- Designed to speed installation for lower installed cost
- Flush tie cut-off limits exposure to sharp edges
- A full line of lightweight, ergonomic hand tools available
- Panduit leads the industry in reliability and performance



#### **Automatic Cable Tie Installation Systems**

- An efficient solution for high volume harnessing, assembly, fastening and packaging applications
- High speed tools lower installed cost and reduce operator fatigue
- Wrap, tension, and cut off cable ties in less than one second
- Microprocessor based controller monitors system performance for production data and reporting

#### **Services**



#### **Custom Imprinting Service**

- Products available for custom imprinting include cable ties, marker plates, marker and flag ties, hook and loop wrap ties
- Results in a professional, high quality appearance for identification and labeling as well as promotional purposes
- Options include company logos, website addresses, sequential numbering, phone numbers, graphics and text

## **Related Products**



#### Cable Accessories

- Comprehensive line of mounts, clips, and clamps that organizes and routes cables, speeds and simplifies installations, and lowers overall installed cost Installation methods include adhesive backed, user applied adhesive, screws, rivets and push barb
- Accessories provide long term reliability while cable clips and clamps offer a one-piece solution to save time and reduce inventory



#### Stainless Steel Cable Ties

- Durable method of bundling, fastening and permanent identification in applications where severe environmental conditions exist
- Engineered for safety, productivity and durability by providing round edges and smooth surfaces, easy threading, high loop tensile strength and tight clamping

