



Get the Best for Your Bench with Mix-or-Match Savings

Save 15% when you buy any 2 (or more) of these Tektronix and Keithley bench instruments

Only Thru Dec. 31
Save 15%

Limited-Time Offer

Save 15% on some of the finest test bench instruments available. Choose any two models (or more) from the series or models on this flyer.

Select from:

- Oscilloscopes
- Digital Multimeters (DMMs)
- Power Supplies
- Arbitrary Function Generators
- DMM/Data Acquisition Systems
- Source Measure Units



New! TBS2000B Digital Storage Oscilloscopes

With six models to choose from and a range of 70 MHz - 200 MHz with up to a 2 GS/s sample rate, these oscilloscopes are suited for today's leading design applications yet affordable enough for student labs.



MSO / DP02000B Oscilloscopes

With more than 12 models to choose from, a range of 70 MHz - 200 MHz and choice of up to 16 (optional) digital channels, these powerful yet affordable oscilloscopes provide advanced debug features and the ability to analyze both analog and digital signals with the same instrument.



All Digital Multimeters & DMM/DAQs

All DMMs and DMM/DAQs, including touchscreen DMM6500 and DAQ6510 with 6.5 digit accuracy and high-speed 1M sample/s digitizing (16-bit).



All Power Supplies

All power supplies, including popular 2220/2230/2231 Series with isolated outputs and remote sensing on all channels.



Source Measure Unit Instruments

Nearly all* Keithley SourceMeter® SMUs, including touchscreen 2450 SMU for intuitive sourcing and measuring current and voltage.



All Arbitrary Function Generators

All Tektronix AFGs, including new AFG31000 with up to 250 MHz bandwidth, 14-bit resolution and up to 2 GS/s sampling with patented InstaView™ technology.

*This program excludes the 2601B-PULSE Pulser/SMU.



Get the Best for Your Bench with Mix-or-Match Savings

Bench Oscilloscopes

| Series | Bandwidth | Channels | Sample Rate |
|--------------------------|--------------|-----------------------------------|------------------|
| TBS2000B Digital Storage | 70 – 200 MHz | 2–4 Analog | 1 GS/s to 2 GS/s |
| MSO2000B / DP02000B | 70 – 200 MHz | 2–4 Analog, 16 Digital (Optional) | 1 GS/s |

Source Measure Unit Instruments*

| Series | Key Features | | |
|--|---------------------------|---|--------------------------------|
| 2400 Series – Bench or Production | 1 Channel Models | Source up to $\pm 10A$ Pulse, $\pm 1100V$, 1000W Touchscreen 2450, 2460, 2461, 2470 | Measure down to 10fA, 100nV |
| 2600B Series – Bench or Production | 1, 2, or 4 Channel Models | Source up to $\pm 10A$ Pulse, $\pm 200V$, 200W | Measure down to 0.1fA, 100nV |
| 2650 Series – High Power <small>*Excludes the 2601B-PULSE Pulser/SMU.</small> | 1 Channel Models | Source up to $\pm 50A$ Pulse, $\pm 3000V$, 2000W | Measure down to 1fA, 1 μ V |

Digital Multimeters

| Category | Models | Key Features |
|---------------------------|----------------------------------|--|
| Basic Performance | DMM6500, 2000, 2110, 2100 | 5½ – 6½ Digit Resolution, 1 – 10 Measurement Channels, Touchscreen DMM6500 |
| High Speed/High Accuracy | DMM7510, DMM7512 | 7½ Digit Resolution, 1 – 2 Measurement Channels, Touchscreen DMM7510 |
| High Accuracy | 2010, 2001, 2002 | 7½ – 8½ Digit Resolution, 1 – 10 Measurement Channels |
| Multi-Channel Measurement | DAQ6510, 2700, 2701, 2750, 3706A | 6½ – 7½ Digit Resolution, 80 – 576 Max Measurement Channels, Touchscreen DAQ6510 |

Power Supplies

| Series | Key Features |
|-----------------------|--|
| PWS4000/Series 2200 | 1-Channel, Low Noise, Programmable |
| Series 2220/2230/2231 | 2–3 Channels, Low Noise, Programmable |
| Series 2260B | 1-Channel, up to 1080W, Programmable |
| Series 2280 | 1-Channel, 6½ digit measure resolution |
| Series 2281 | 1-Channel, Dynamic Battery Simulator |

Arbitrary Function Generators

| Series | Bandwidth | Record Length |
|----------|------------------|-----------------------|
| AFG1000 | 25 MHz – 60 MHz | 8k points – 1M points |
| AFG2000 | 20 MHz | 128k points |
| AFG3000 | 10 MHz – 150 MHz | 128k points |
| AFG31000 | 25 MHz – 250 MHz | 16 MSa/ch |



Learn about our promotion on 3 Series MD0, 4 Series MSO and 5 Series MSO oscilloscopes.

Offer Ends
December 31, 2020

www.tek.com
www.tek.com/keithley

Terms and Conditions

- Not all included models listed here; contact your Tektronix representative for the complete listing.
- This program excludes the 2601B-PULSE Pulser/SMU.
- The customer's purchase order must be booked between Oct. 1, 2020 and Dec. 31, 2020. Any quote with this program discount after the end date will not qualify.
- Offer applies to new products sales only, including GSA, Encore, demo, or used products do not qualify.
- This program can be combined with an education discount, but not CFI.
- Offer cannot be combined with any other programs including registration or other promotions unless otherwise noted.
- Tektronix reserves the right to change or cancel this program at any time.



46W-67744-0

Copyright © 2020, Tektronix. All rights reserved. Tektronix and Keithley products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX, TEK and Keithley are registered trademarks of Tektronix, Inc.

